

V Shape

Body shaping equipment

● Application






- Wrinkle removal
- Skin lifting
- Skin tightening
- Skin surface smooth
- Eyelid area treatment
- Body shaping
- Body slimming
- Cellulite reduction
- Massage
- Body circumference reduction

● Advantage


- AM-8 Shape & Smooth features revolutionary combination of bipolar radio frequency, near-infrared laser, pulse mechanical tissue manipulation;
- The safety and effectiveness of the technology of AM-8 have been demonstrated in body contouring and wrinkle removal on any parts of human body;
- Perfect result with combining five technology together, to get the body shaping, skin tightening, wrinkle removal expect.
- AM-8 Shape & Smooth is the example of perfect combining ALUMA of American LUMENIS company with VELASHAPE of Israel Syneron company.

AM-8

www.aesmedlaser.com



• Working Principle



- 40k handle produces huge cavity phenomenon (bubble) inside fatty tissue and broken part of cell membrane finally. The ultrasound energy heats the fat tissue layer and stimulates the fat cells to release their lipid content without rupturing the cell membrane. Then push the lipids (inclusion and hangover) away from the fat cells and into the lymphatic system.
- No.2 & No.3 handle technology principle. These two handles are powered by RF, Near Infrared laser, Vacuum, Rollers. First Vacuum lift the aimed skin, then 940nm Laser directly heat efficiency to the muscle and arthrosis, with the temperature rise up, it could highly reduce the impedance for energy transferring. At the same time RF energy start to melt the fat cells, restructure the rough surface skin, speed up human being's metabolism, impel the liquid fat to outflow away from fat cell and be matabolized out of the body, so as to get ideal result of body shaping and slimming. Rollers have a massage effect for the surface and dermis tissue, to make skin look more smooth and tightened.
- The small handle is designed for face anti aging use. Technology include RF, vacuum and Near Infrared laser. Vacuum lift skin on face or around eye area. RF and NIL act on the surface and dermis tissue, to clear the dead and old cells in the dermis and stimulate the collagen rebirth.

• Technical Specification

Laser: 940nm tripolar rf vacuum cavitation machine

Applicator tips: 5

Net weight: 55kg

Cavitation: 40K

RF frequency: 1 MHz

Rollers speed: 0-36rpm

Laser power: Max 20 W

Wireless IC card management

Rollers working mode: 1 type tripolar rf vacuum cavitation machine

Safety Testing Mode: Real-time online

Energy Density of RF: Max 60J/ c m³

Rated input voltage: AC230±10%, 50Hz±1Hz/

AC110V±10%, 60Hz±1Hz (optional)

Physical dimensions: 625mm*525mm*1070mm

Treatment area of handpiece:

4mm*7mm/ 8mm*25mm/30mm*50mm/40mm*60mm

• Treatment Handles



NO.1 HANDPIECE



NO.2 HANDPIECE



NO.3 HANDPIECE



NO.4 HANDPIECE



40k CAVITATION

